



700 mm

14 mm Perforation

14 mm Perforation

20 mm No Printing Area
 Solid colour background required with high contrast vs. eye marking spot
 No graphics, no text (one background colour only) and no transparency in this area.

BACK FACE

310 mm

Winding Direction

Eyemark 20x5
20 mm

45 mm
UFI Field
 15 mm

10 mm

10 mm

BOTTOM

bottom printed with 1x white = 50 % opacity

FRONT FACE

Henkel blue always should be used for bottom eyemark



20 mm No Printing Area
 Solid colour background required with high contrast vs. eye marking spot
 No graphics, no text (one background colour only) and no transparency in this area.

UFI Field

BOTTOM
 bottom printed with 1x white = 50 % opacity

Henkel blue always should be used for bottom eyemark

Eyemark 20x5
20 mm

310 mm

700 mm

14 mm Perforation

14 mm Perforation

BACK FACE

FRONT FACE

Winding Direction